






- NOTES:
- 1. SUBSTRATE:
LIBA2000+
 - 2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: NONE
S2: NONE
 - 3. CENTERING: ≤25 ARCMIN



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm	18.00	 Edmund Optics®		
			BFL @ 587.6nm	10.50			
SHAPE	CONVEX	PLANO			TITLE	26.5mm Dia. x 18mm FL, Uncoated, Molded Condenser Lens with Smooth Diffuser	
SURFACE QUALITY	AS MOLDED	SMOOTH DIFFUSER					
CLEAR APERTURE	Ø 21.60	Ø 21.60	ALL DIMS IN	mm	DWG NO	22680	SHEET 1 OF 1
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					