





- NOTES:
- 1. SUBSTRATE:  
LIBA2000+
  - 2. COATING (APPLY ACROSS CLEAR APERTURE)  
  
S1: NONE  
S2: NONE
  - 3. CENTERING: ≤25 ARCMIN



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm	28.50	 <b>Edmund Optics®</b>		
			BFL @ 587.6nm	16.90			
SHAPE	CONVEX	PLANO	THIRD ANGLE PROJECTION 	TITLE	40mm Dia. x 28.5mm FL, Uncoated, Molded Condenser Lens with Smooth Diffuser		
SURFACE QUALITY	AS MOLDED	SMOOTH DIFFUSER					
CLEAR APERTURE	Ø 32.40	Ø 32.40					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	22683	SHEET 1 OF 1