


NOTES:

1. COATING (APPLY ACROSS COATING APERTURE)

DURABILITY: MIL-C-48497A
PERFORMANCE SPECIFICATIONS:
CWL: 635
FWHM: 16 NOMINAL
TRANSMISSION %: 84% (400-600nm); 85% (700-1500)

2. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS
APPLY ACROSS CLEAR APERTURE

3. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® Edmund Optics®

S1		S2		<div>THIRD ANGLE PROJECTION</div>		TITLE		635nm 70 x 375mm META® holoOPTIX® FLEX Notch Filter	
SHAPE	PLANO		PLANO	ALL DIMS IN	mm	DWG NO	23035	SHEET 3 OF 3	