


# UV-AR Coating Curve

Coating Specification:  $R_{\text{abs}} \leq 1.0\%$  @ 250 - 425nm,  $R_{\text{avg}} \leq 0.75\%$  @ 250 - 425nm,

$R_{\text{avg}} \leq 0.5\%$  @ 370 - 420nm

Damage Threshold, Reference: 3 J/cm<sup>2</sup> @ 355nm, 10ns

Theoretical Reflection Curve



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED