



NOTES:

- 1. SUBSTRATE:  
N-BK7
- 2. COATING (APPLY ACROSS CLEAR APERTURE)  
  
S1 & S2: NONE
- 3. FINE GROUND SURFACE
- 4. POWER, IRREGULARITY, AND SURFACE QUALITY  
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
- 5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                 |                     |                     |                                                                                       |       |                                                                                                             |                                                                             |                 |
|-----------------|---------------------|---------------------|---------------------------------------------------------------------------------------|-------|-------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------|-----------------|
|                 | S1                  | S2                  | EFL                                                                                   | 25.00 |  <b>Edmund Optics®</b> |                                                                             |                 |
| SHAPE           | CONVEX              | PLANO               | BFL                                                                                   | 23.02 |                                                                                                             |                                                                             |                 |
| RADIUS          | 12.92               | ∞                   |  |       | TITLE                                                                                                       | 20mm H x 40mm L x 25mm FL Uncoated,<br>Illumination Grade PCX Cylinder Lens |                 |
| SURFACE QUALITY | 60 - 40             | 60 - 40             |                                                                                       |       |                                                                                                             |                                                                             |                 |
| CLEAR APERTURE  | 19.00 x 39.00       | 19.00 x 39.00       |                                                                                       |       | DWG NO                                                                                                      | 25492                                                                       | SHEET<br>4 OF 8 |
| BEVEL           | PROTECTED AS NEEDED | PROTECTED AS NEEDED | ALL DIMS IN                                                                           | mm    |                                                                                                             |                                                                             |                 |