


NOTES:

- 1. SUBSTRATE:
FUSED SILICA
- 2. S2 TO BE PARALLEL WITH S1 TO <1 arcsec
- 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1&S2: Rabs ≤0.25% @ 880nm
Ravg ≤1.25% @ 400 - 870nm
Ravg ≤1.25% @ 890 - 1000nm NONE

4. FINE GRIND SURFACE

5. ROHS COMPLIANT




FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
WAVELENGTH RANGE (nm)	400 - 1000	400 - 1000
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE
PROJECTION



ALL DIMS IN

mm



Edmund Optics®

TITLE

25mm Diameter VIS-NIR Coated, Ultra Thin
Fused Silica Window

DWG NO

24245

SHEET
15 OF 15