



NOTES:

- 1. COATING:  
S1: MAXIBLACK™  
THICKNESS: 4 - 6 (µm)
- 2. ABSORBANCE: 98 %
- 3. ABRASION RESISTANCE: MODERATE
- 4. HUMIDITY RESISTANCE: MIL-C-48497A
- 5. OPERATING TEMPERATURE (°C): -40 to 121
- 6. WAVELENGTH RANGE(µm): 0.3 - 5




DETAIL A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**EO**® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	10 x 10cm Sheet of MaxiBlack Foil, Standard Adhesive	
ALL DIMS IN	mm	DWG NO	28944	SHEET 1 OF 1