




- NOTES:
- 1. SUBSTRATE: Polymer Film XP40HT-18
 - 2. WAVELENGTH RANGE: 400 - 700 nm
 - 3. POLARIZATION EFFICIENCY (%): >99.5
 - 4. TRANSMISSION (%):
 - SINGLE: 40 ±2
 - PARALLEL: 32.2
 - CROSSED: <0.005
 - 5. EXTINCTION RATIO: 5000:1
 - 6. TEMPERATURE RESISTANCE (°C x HOURS):
 - HEAT: 100 x 1,000
 - COLD: -40 x 1,000
 - HUMIDITY: 80 x 90% RH x 1,000
 - 7. ROHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	600 x 1000mm High Temperature Linear Polarizing Film (XP40HT-18) with Adhesive
ALL DIMS IN	mm	DWG NO	29463
			SHEET 23 OF 50