





NOTES:

- 1. SUBSTRATE:
TAC FILM
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: NONE
- 3. PROTECTIVE FILM ON NON-MATTE SURFACE SHOULD BE REMOVED BEFORE USE
- 4. WAVELENGTH RANGE: 300 - 1100nm
- 5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

THIRD ANGLE PROJECTION 		 Edmund Optics®		
TITLE		12.5mm Diameter Light Diffusing Film		
ALL DIMS IN	mm	DWG NO	27086	SHEET 29 OF 86