




NOTES:

1. SUBSTRATE:
TAC FILM
2. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: NONE
3. PROTECTIVE FILM ON NON-MATTE SURFACE SHOULD BE REMOVED BEFORE USE
4. WAVELENGTH RANGE: 300 - 1100nm
5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

THIRD ANGLE PROJECTION 		 Edmund Optics®		
TITLE		25mm Diameter Light Diffusing Film		
ALL DIMS IN	mm	DWG NO	27089	SHEET 30 OF 86