




NOTES:


1. CUT-ON WAVELENGTH: 825±16.5nm
2. BLOCKING RANGE: 694.2 - 796.4nm
3. TRANSMISSION RANGE: >85% @ 854.1 - 1100nm
4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION 	TITLE	825nm 12.45mm, Ultra-Thin OD 4.0 Longpass Filter		
ALL DIMS IN	mm	DWG NO	29197	SHEET 11 OF 24