




NOTES:


- 1. CUT-ON WAVELENGTH: 500±10.0nm
- 2. BLOCKING RANGE: 517.7 - 575.8nm
- 3. TRANSMISSION RANGE: >85% @ 400 - 482.7nm
- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	500nm 12.45mm, Ultra-Thin OD 4.0 Shortpass Filter	
ALL DIMS IN	mm	DWG NO	29200	SHEET 14 OF 24