




NOTES:


- 1. CUT-ON WAVELENGTH: 550±11.0nm
- 2. BLOCKING RANGE: 569.4 - 633.3nm
- 3. TRANSMISSION RANGE: >85% @ 400 - 530.9nm
- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	550nm 12.45mm, Ultra-Thin OD 4.0 Shortpass Filter	
ALL DIMS IN	mm	DWG NO	29201	SHEET 15 OF 24