




NOTES:


- 1. CUT-ON WAVELENGTH: 650±13.0nm
- 2. BLOCKING RANGE: 672.9 - 748.5nm
- 3. TRANSMISSION RANGE: >85% @ 400 - 627.4nm
- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	650nm 12.45mm, Ultra-Thin OD 4.0 Shortpass Filter	
ALL DIMS IN	mm	DWG NO	29204	SHEET 18 OF 24