


NOTES

1. SUBSTRATE: N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1 & S2: NONE
3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN <1 ARCMIN

4. FINE GRIND SURFACE



5. TRANSMITTED WAVEFRONT DISTORTION:  $\leq 0.25$  WAVE @632.8nm

6. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2					
SHAPE	PLANO	PLANO	<div>THIRD ANGLE PROJECTION</div> 	TITLE		25 x 35mm, 3mm Thick, Uncoated λ/4 N-BK7 Window	
SURFACE QUALITY	60 - 40	60 - 40		DWG NO		29301	
CLEAR APERTURE	22.50 x 31.50	22.50 x 31.50				SHEET 1 OF 1	
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm			