




NOTES:

- 1. SUBSTRATE:  
FUSED SILICA
- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO 30 ARCSEC
- 3. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: UV ENHANCED SILVER (350 - 3,000nm)  
R(AVG) >90% @ 350 - 400nm  
R(AVG) >96% @ 400 - 3,000nm
- S2: NONE



4. FINE GRIND SURFACE

- 5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2			 Edmund Optics®		
SHAPE	PLANO	PLANO		TITLE	15mm Diameter UV Enhanced Silver Coated, λ/10 Mirror		
SURFACE QUALITY	20 - 10	COMMERCIAL POLISH		DWG NO 70235			
SURFACE FLATNESS	λ/10 (BEFORE COATING)	N/A					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm		SHEET 3 OF 9	