




NOTES:

- 1. SUBSTRATE:
FUSED SILICA
- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO 30 ARCSEC
- 3. COATING (APPLY ACROSS CLEAR APERTURE)
S1: UV ENHANCED SILVER (350 - 3,000nm)
R(AVG) >90% @ 350 - 400nm
R(AVG) >96% @ 400 - 3,000nm
- S2: NONE



4. FINE GRIND SURFACE

- 5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2			 Edmund Optics®	
SHAPE	PLANO	PLANO	<div>THIRD ANGLE PROJECTION</div> 	TITLE	20mm Diameter UV Enhanced Silver Coated, λ/10 Mirror	
SURFACE QUALITY	20 - 10	COMMERCIAL POLISH				
SURFACE FLATNESS	λ/10 (BEFORE COATING)	N/A				
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	70236
					SHEET 4 OF 9	