


- NOTES:
- 1. SUBSTRATE:
PMMA, PERMANENTLY LAMINATED TO PET FILM WITH HARD MICROSTRUCTURED POLYMER COATING
 - 2. TYPE OF DIFFUSER: Linear Batwing Diffuser
 - 3. DIFFUSING ANGLE (°): 127
 - 4. OPERATING TEMPERATURE (°C): -34 to +70
 - 5. FOR OPTIMAL PERFORMANCE, GLOSSY, NON-MATTE SIDE SHOULD FACE INCIDENT LIGHT.



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 		TITLE	50mm Dia., 127° Diffusion Angle, Linear Batwing Diffuser	
ALL DIMS IN	mm	DWG NO	70773	SHEET 7 OF 11