







- NOTES:
- 1. SUBSTRATE: FLOAT GLASS
 - 3. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1 & S2: BBAR (425-700nm)
 - R(AVG) ≤0.5% @ 425 - 700nm

-  FINE GRIND SURFACE
- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

		S1	S2	 Edmund Optics®		
SHAPE		PLANO	PLANO		TITLE	101.6 x 101.6 x 2mm High Efficiency Window
SURFACE QUALITY		80 - 50	80 - 50			
CLEAR APERTURE		91.44 x 91.44	91.44 x 91.44	ALL DIMS IN	DWG NO	
BEVEL		PROTECTED AS NEEDED	PROTECTED AS NEEDED	mm	71598	SHEET 3 OF 4