

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Ring Lights](#)

Advanced Illumination Standard Working Distance LED Ring Lights


See More by [Advanced Illumination](#)



- 4" Working Distance
- Provides 1.7" Coverage
- Variable Intensity and Strobed Options

Technical Information

Products

Color	Wavelength (nm)	Dia. (mm)	Illumination Mode	Inner Diameter (mm)	Stock Number	Price	Buy
#66-774 Clearance							
							
Clearance							
Availability is limited, so buy before these products disappear. Sorry, we cannot accept returns. Receive up to 80% off select products.							
White	-	85.00	Constant	55.4		₹35,231	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038
Phone: 1-800-363-1992 :
www.edmundoptics.com