

[All Products](#) / [Testing and Detection](#) / [Detectors](#)

## Segmented InGaAs Photodiodes



- Four Individual Active Area Elements
- High Response Uniformity and Low Crosstalk
- Ideal for Position Detection and Beam Alignment
- [Segmented Silicon Photodiodes](#) and [InGaAs Photodiodes](#) Also Available

### Common Specifications

#### Physical & Mechanical Properties

Element Gap (mm):	0.045
-------------------	-------

#### Electrical

Responsivity @ 1310nm (AW):	0.85 minimum / 0.9 typical
-----------------------------	----------------------------


Responsivity @ 1550nm (AW):	0.9 minimum / 0.95 typical
-----------------------------	----------------------------

#### Environmental & Durability Factors

Operating Temperature (°C):	-40 to +75
-----------------------------	------------

Storage Temperature (°C):	-55 to +125
---------------------------	-------------

## Technical Information



## Products

Size of Active Area (mm)	Connector	Stock Number	Price	Buy
1 Dia.	TO-5	<a href="#">#17-077</a>	₹26,550 Qty 5+ ₹23,760	Contact Us
3 Dia.	TO-8	<a href="#">#17-078</a>	₹54,450 Qty 5+ ₹48,150	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)