


[All Products](#) / [Optics](#) / [Optical Lenses](#) / [Aspheric Lenses](#) / [Glass Polished](#)
TECHSPEC® Double-Sided Aspheric Lenses


- Designed for 1X Magnification
- Ideal for Finite Conjugate Applications
- 10 to 50mm Diameter Options

Common Specifications


Physical & Mechanical Properties

Centering (arcmin):	<3	Edge Thickness ET (mm):	5
Bevel:	None		

Optical Properties

Substrate:	N-BK7		
Aspheric Design Wavelength (nm):	587.6	Asphere Figure Error, RMS @ 632.8nm:	0.4λ RMS and 2λ PV
Coating:	Uncoated	Surface Quality:	40-20
f/#:	1.00	Wavelength Range (nm):	330 - 2400

Technical Information



Products

Dia. (mm)	EFL (mm)	Coating	Stock Number	Price	Buy
10.00	10.00	Uncoated	#18-414	₹22,654 Qty 6+ ₹18,139	10 to 12 days
12.50	12.50	Uncoated	#18-417	₹27,092 Qty 6+ ₹21,720	10 to 12 days
25.00	25.00	Uncoated	#18-420	₹36,823 Qty 6+ ₹29,505	10 to 12 days
50.00	50.00	Uncoated	#18-423	₹58,388 Qty 6+ ₹46,710	10 to 12 days



Copyright 2023, Edmund Optics India Private Limited, #267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038

Phone: 1-800-363-1992 :

www.edmundoptics.com