

[See all 12 Products in Family](#)

Optotune -2 to +3 Diopter, M25.5 x 0.5 to M40.5 x 0.5 Focus Tunable Lens | EL-16-40-TC-VIS-5D-M25.5

See More by [Optotune](#)



Stock **#33-491** **1 In Stock**

-

1

+

MRP ₹1,27,440

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,27,440 each
Need More?	Request Quote

Product Downloads

General	
Specialty Lens	Type:
#88-940	Driver:
1,000,000,000	Lifecycles:
	Model Number:

EL-16-40-TC-VIS-5D-M25.5	
5 (typical @ 30°C)	Response Time (ms):
25 (typical @ 30°C)	Settling Time (ms):
Physical & Mechanical Properties	
16.00	Clear Aperture CA (mm):
47.0 x 70.0	Dimensions (mm):
17.60	Thickness (mm):
Optical Properties	
Low Dispersion Polymer	Substrate: □
BBAR (420-950nm)	Coating:
420 - 950	Wavelength Range (nm):
100.00	Abbe Number (v _d):
-2 to +3 diopter -500 to +333mm	Focus Range (mm):
1.3	Index of Refraction (n _d):
Transmitted Wavefront Error, RMS: Vertical: 0.25λ @ 525nm Horizontal: 0.50λ @ 525nm	
Electrical	
-250 to 250	Current (mA):
0 - 0.7	Power Consumption (W):
Threading & Mounting	
M25.5 x 0.5 (Male) M40.5 x 0.5 (Female)	Mounting Threads:
Environmental & Durability Factors	
-20 to +65	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 251:
Slovakia	Country of Origin:
Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Product Details

- Multiple Imaging Lens Mounting Options
- Large Clear Aperture Ideal for Machine Vision Applications
- Industrial Hirose Connection with Temperature Sensing
- Integrated Temperature Control for Improved Thermal Effects
- [Optotune Focus Tunable Lenses 10mm Clear Aperture Hirose Connector](#) and [Lens Drivers](#) Also Available

Optotune Focus Tunable Lenses 16mm Clear Aperture Hirose Connector eliminate the need for optomechanical subsystems otherwise required to alter the focal length of your imaging application. They feature large clear apertures and are offered in many popular machine vision mounting options, making them ideal for inspection and detection systems. These lenses offer continuous focusability from -2 to +3 diopters controlled by an industrial Hirose connection. Optotune Focus Tunable Lenses 16mm Clear Aperture Hirose Connector exhibit no autofluorescence, reducing unwanted light on the detector and feature integrated temperature sensing to provide open loop reproducibility typically within 0.1 diopters. The lenses are made of low dispersion polymer and feature a broadband anti-reflection coating.

Note: Hirose cables, available in 1m length ([#88-941](#)), 3m length ([#33-468](#)) or 5m length ([#23-852](#)), and Lens Driver ([#88-940](#)) are required and sold separately. The Gardasoft TR-CL180 Industrial Lens Controller ([#13-803](#)) is an optional accessory that provides repeatable, precision control of Optotune Industrial Focus-Tunable Lenses. Prescription data is available to model the effect an offset lens has on overall focal range.

Technical Information

