

[See all 12 Products in Family](#)

# Optotune -2 to +3 Diopter, M27 x 0.5 to M40.5 x 0.5 Focus Tunable Lens | EL-16-40-TC-VIS-5D-M27

See More by [Optotune](#)



Stock **#33-492** **4 In Stock**

-

1

+

MRP ₹1,27,440

 Price inclusive of all taxes

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹1,27,440 each                |
| Need More?     | <a href="#">Request Quote</a> |

| Product Downloads |
|-------------------|
|-------------------|

| General                 |               |
|-------------------------|---------------|
| Specialty Lens          | Type:         |
| <a href="#">#88-940</a> | Driver:       |
| 1,000,000,000           | Lifecycles:   |
|                         | Model Number: |

|                                                                                                                                                                                                                         |                                        |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------|
| EL-16-40-TC-VIS-5D-M27                                                                                                                                                                                                  |                                        |
| 5 (typical @ 30°C)                                                                                                                                                                                                      | Response Time (ms):                    |
|                                                                                                                                                                                                                         |                                        |
| 25 (typical @ 30°C)                                                                                                                                                                                                     | Settling Time (ms):                    |
|                                                                                                                                                                                                                         |                                        |
| Physical & Mechanical Properties                                                                                                                                                                                        |                                        |
| 16.00                                                                                                                                                                                                                   | Clear Aperture CA (mm):                |
|                                                                                                                                                                                                                         |                                        |
| 47.0 x 70.0                                                                                                                                                                                                             | Dimensions (mm):                       |
|                                                                                                                                                                                                                         |                                        |
| 17.60                                                                                                                                                                                                                   | Thickness (mm):                        |
|                                                                                                                                                                                                                         |                                        |
| Optical Properties                                                                                                                                                                                                      |                                        |
| Low Dispersion Polymer                                                                                                                                                                                                  | Substrate: □                           |
|                                                                                                                                                                                                                         |                                        |
| BBAR (420-950nm)                                                                                                                                                                                                        | Coating:                               |
|                                                                                                                                                                                                                         |                                        |
| 420 - 950                                                                                                                                                                                                               | Wavelength Range (nm):                 |
|                                                                                                                                                                                                                         |                                        |
| 100.00                                                                                                                                                                                                                  | Abbe Number (v <sub>d</sub> ):         |
|                                                                                                                                                                                                                         |                                        |
| -2 to +3 diopter<br>-500 to +333mm                                                                                                                                                                                      | Focus Range (mm):                      |
|                                                                                                                                                                                                                         |                                        |
| 1.3                                                                                                                                                                                                                     | Index of Refraction (n <sub>d</sub> ): |
|                                                                                                                                                                                                                         |                                        |
| Transmitted Wavefront Error, RMS:<br>Vertical: 0.25λ @ 525nm<br>Horizontal: 0.50λ @ 525nm                                                                                                                               |                                        |
| Electrical                                                                                                                                                                                                              |                                        |
| -250 to 250                                                                                                                                                                                                             | Current (mA):                          |
|                                                                                                                                                                                                                         |                                        |
| 0 - 0.7                                                                                                                                                                                                                 | Power Consumption (W):                 |
|                                                                                                                                                                                                                         |                                        |
| Threading & Mounting                                                                                                                                                                                                    |                                        |
| M27 x 0.5 (Male)<br>M40.5 x 0.5 (Female)                                                                                                                                                                                | Mounting Threads:                      |
|                                                                                                                                                                                                                         |                                        |
| Environmental & Durability Factors                                                                                                                                                                                      |                                        |
| -20 to +65                                                                                                                                                                                                              | Operating Temperature (°C):            |
|                                                                                                                                                                                                                         |                                        |
| Regulatory Compliance                                                                                                                                                                                                   |                                        |
| Compliant                                                                                                                                                                                                               | RoHS 2015:                             |
|                                                                                                                                                                                                                         |                                        |
| View                                                                                                                                                                                                                    | Certificate of Conformance:            |
|                                                                                                                                                                                                                         |                                        |
| Compliant                                                                                                                                                                                                               | Reach 251:                             |
|                                                                                                                                                                                                                         |                                        |
| Slovakia                                                                                                                                                                                                                | Country of Origin:                     |
|                                                                                                                                                                                                                         |                                        |
| Imported By:<br>Edmund Optics India Private Limited<br>267, Greystone Building, Second Floor,<br>6th Cross Rd, Binnamangala,<br>Stage 1, Indiranagar, Bengaluru,<br>Karnataka, India 560038<br>Phone: +91- 80-6845 0000 |                                        |

## Product Details

- Multiple Imaging Lens Mounting Options
- Large Clear Aperture Ideal for Machine Vision Applications
- Industrial Hirose Connection with Temperature Sensing
- Integrated Temperature Control for Improved Thermal Effects
- [Optotune Focus Tunable Lenses 10mm Clear Aperture Hirose Connector](#) and [Lens Drivers](#) Also Available

Optotune Focus Tunable Lenses 16mm Clear Aperture Hirose Connector eliminate the need for optomechanical subsystems otherwise required to alter the focal length of your imaging application. They feature large clear apertures and are offered in many popular machine vision mounting options, making them ideal for inspection and detection systems. These lenses offer continuous focusability from -2 to +3 diopters controlled by an industrial Hirose connection. Optotune Focus Tunable Lenses 16mm Clear Aperture Hirose Connector exhibit no autofluorescence, reducing unwanted light on the detector and feature integrated temperature sensing to provide open loop reproducibility typically within 0.1 diopters. The lenses are made of low dispersion polymer and feature a broadband anti-reflection coating.

**Note:** Hirose cables, available in 1m length ([#88-941](#)), 3m length ([#33-468](#)) or 5m length ([#23-852](#)), and Lens Driver ([#88-940](#)) are required and sold separately. The Gardasoft TR-CL180 Industrial Lens Controller ([#13-803](#)) is an optional accessory that provides repeatable, precision control of Optotune Industrial Focus-Tunable Lenses. Prescription data is available to model the effect an offset lens has on overall focal range.

Technical Information

