

[See all 75 Products in Family](#)

# LightPath 354430 | 2mm Dia., 0.15 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#48-145** **20+ In Stock**

⊖ 1 ⊕ MRP ₹8,576

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹8,576 each
Qty 11-49	₹7,718 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

354430 **Lightpath Lens Code:**

Aspheric Lens **Type:**

Collimate or Focus Laser Light **Typical Applications:**

### Physical & Mechanical Properties

2.00 ±0.015	<b>Diameter (mm):</b>
1.6	<b>Clear Aperture CA (mm):</b>
0.86	<b>Edge Thickness ET (mm):</b>
1.01 ±0.05	<b>Center Thickness CT (mm):</b>
Protective as needed	<b>Bevel:</b>

## Optical Properties

5.00 @ 1550nm	<b>Effective Focal Length EFL (mm):</b>
0.15	<b>Numerical Aperture NA:</b>
<b>D-ZK3</b>	<b>Substrate:</b> <input type="checkbox"/>
±1	<b>Focal Length Tolerance (%):</b>
1550	<b>Aspheric Design Wavelength (nm):</b>
BBAR (600-1050nm)	<b>Coating:</b>
$R_{avg} < 1.0\%$ @ 600 - 1050nm	<b>Coating Specification:</b>
40-20	<b>Surface Quality:</b>
3.33	<b>f#:</b>
50.22	<b>Abbe Number (<math>v_d</math>):</b>
1.603	<b>Index of Refraction (<math>n_d</math>):</b>
600 - 1050	<b>Wavelength Range (nm):</b>
4.37	<b>Working Distance (mm):</b>
Infinite	<b>Conjugate Distance:</b>
1550.00	<b>Focal Length Specification Wavelength (nm):</b>
< 0.17	<b>Transmitted Wavefront Error (<math>\lambda</math>, RMS):</b>

## Material Properties

11.1	<b>Coefficient of Thermal Expansion CTE (<math>10^{-6}/^{\circ}\text{C}</math>):</b>
------	--

## Environmental & Durability Factors

≤200	<b>Operating Temperature (<math>^{\circ}\text{C}</math>):</b>
------	---

## Regulatory Compliance

<b>Compliant</b>	<b>RoHS 2015:</b>
<b>View</b>	<b>Certificate of Conformance:</b>
<b>Compliant</b>	<b>Reach 247:</b>
China	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Eliminate Spherical Aberration

- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



## Technical Information

