

[See all 76 Products in Family](#)

LightPath 354260 | 6.5mm Dia., 0.16 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#37-099** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ MRP ₹8,576

📌 Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-10 | ₹8,576 each |
| Qty 11-49 | ₹7,718 each |
| Need More? | Request Quote |

Product Downloads

General

Thickness: 0.25 (t) (mm)
Material: BK7

Compatible Window:

354260

Lightpath Lens Code:

Aspheric Lens

Type:

Typical Applications:
Collimate or Focus Laser Light

Physical & Mechanical Properties

Diameter (mm):
6.50 ±0.015

Clear Aperture CA (mm):
5

Edge Thickness ET (mm):
1.8

Center Thickness CT (mm):
2.21 ±0.05

Bevel:
Protective as needed

Distance from Window to Lens (D) (mm):
12.727

Optical Properties

Effective Focal Length EFL (mm):
15.29 @ 780nm

Numerical Aperture NA:
0.16

Substrate:
[D-ZK3](#)

Focal Length Tolerance (%):
±1

Aspheric Design Wavelength (nm):
780

Coating:
BBAR (600-1050nm)

Coating Specification:
R_{abs} <1.0% @ 600 - 1050nm

Surface Quality:
40-20

f#:
3.12

Abbe Number (v_d):
50.22

Index of Refraction (n_d):
1.586

Wavelength Range (nm):
600 - 1050

Working Distance (mm):
13.98

Conjugate Distance:
Infinite

Focal Length Specification Wavelength (nm):
780.00

Transmitted Wavefront Error (λ, RMS):
< 0.09

Material Properties

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
7.6

Environmental & Durability Factors

Operating Temperature (°C):
≤200

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)

Country of Origin:
China

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000


Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information



Compatible Mounts