

[See all 76 Products in Family](#)

LightPath 354560 | 6.33mm Dia., 0.18 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#83-556** **20+ In Stock**

1 MRP ₹8,576

1 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹8,576 each
Qty 11-49	₹7,718 each
Need More?	Request Quote

Product Downloads

General

354560 **Lightpath Lens Code:**
Aspheric Lens **Type:**

Collimate or Focus Laser Light **Typical Applications:**

Physical & Mechanical Properties

6.33 ±0.015	Diameter (mm):
5.10	Clear Aperture CA (mm):
2.28	Edge Thickness ET (mm):
2.77 ±0.05	Center Thickness CT (mm):
Protective as needed	Bevel:

Optical Properties

13.90 @650nm	Effective Focal Length EFL (mm):
0.18	Numerical Aperture NA:
D-ZK3	Substrate: <input type="checkbox"/>
±1	Focal Length Tolerance (%):
650	Aspheric Design Wavelength (nm):
BBAR (350-700nm)	Coating:
R _{avg} <0.5% @ 350 - 700nm	Coating Specification:
40-20	Surface Quality:
2.78	f#:
60.88	Abbe Number (v_d):
1.586	Index of Refraction (n_d):
350 - 700	Wavelength Range (nm):
12.11	Working Distance (mm):
Infinite	Conjugate Distance:
650.00	Focal Length Specification Wavelength (nm):
< 0.07	Transmitted Wavefront Error (λ, RMS):

Material Properties

7.6	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
-----	---

Environmental & Durability Factors

≤200	Operating Temperature (°C):
------	------------------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
China	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available

- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information

