

## 0.22" Travel, XYZ Axes, Extended Travel, Micro Series (A)



Stock #56-421 **1 In Stock**

1 MRP ₹1,00,890

● Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹1,00,890 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

English **Type:**  
Without Covered Rails **Note:**

### Physical & Mechanical Properties

Linear (X-Y-Z) **Type of Movement:**

Ball Bearing	<b>Guide System:</b>
Center Drive	<b>Drive Orientation:</b>
11.2 x 26.2	<b>Stage Size (mm):</b>
5.6	<b>Travel (mm):</b>
0.22	<b>Travel (inches):</b>
0.155" (3.9mm) Thru with 8-32 TPI Threaded	<b>Center Hole:</b>
Aluminum Body, Stainless Steel Rails	<b>Construction:</b>
0.25	<b>Load Capacity, Normal (kg):</b>
0.44 x 1.03	<b>Stage Size (inches):</b>
1.5	<b>Straight Line Accuracy (µm):</b>
7.5	<b>Weight (g):</b>
<b>Optical Properties</b>	
0.01	<b>Wobble (mrad):</b>
<b>Hardware &amp; Interface Connectivity</b>	
Fine Screw (80 Pitch)	<b>Type of Drive:</b>
<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>REACH 241:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>


## Product Details

- Two Micro Sizes Available
- Versions with Covered Rails
- Three Travel Selections
- X, XY, and XYZ Axis Models


These stages are a dimensional breakthrough and the smallest positioners available today. Positive spring loaded carriage provides precise, smooth motion with no backlash. Straight line accuracy under 2 microns. Features fine 80 TPI lead screw drive. The larger series, Stage Size B, are for longer travel, higher load applications. Fully metric compatible clearance holes. Covered Rail versions are slightly wider, but offer protection for the guide rails. Accessories allow for mounting our precision pinholes for spatial filtering applications. Anodized aluminum construction with stainless rails.

## Technical Information

Manual Micro Positioning Stage #56-421



NOTE:  
1. CENTER OF .220 INCH TOTAL  
TRAVEL X,Y,Z



Units: inches