

[See all 76 Products in Family](#)

LightPath 355440 | 4.7mm Dia., 0.50 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-134** CLEARANCE **17 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ MRP ₹8,576

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹8,576 each
Need More?	Request Quote

Product Downloads

General

Thickness: 0.25 (t) (mm)
Material: BK7

Compatible Window:

355440

Lightpath Lens Code:

Aspheric Lens

Type:

Typical Applications:

Note:

NA, Object (mm): 0.26
 WD, Image (mm): 7.09
 WD, Object (mm): 2.71

Physical & Mechanical Properties

Diameter (mm):
 4.70 ±0.020

Clear Aperture CA (mm):
 4.12

Edge Thickness ET (mm):
 2.68

Center Thickness CT (mm):
 3.83 ±0.05

Bevel:

Protective as needed

Distance from Window to Lens (D) (mm):
 1.962

Optical Properties

Effective Focal Length EFL (mm):
 2.76 @ 980nm

Numerical Aperture NA:
 0.50

Substrate:

[D-ZLaF52LA](#)

Focal Length Tolerance (%):
 ±1

Aspheric Design Wavelength (nm):
 980

Coating:
 BBAR (600-1050nm)

Coating Specification:
 R_{abs} <1.0% @ 600 - 1050nm

Surface Quality:
 40-20

f#:
 0.96

Abbe Number (v_d):
 40.79

Index of Refraction (n_d):
 1.806

Wavelength Range (nm):
 600 - 1050

Working Distance (mm):
 7.09

Conjugate Distance:
 Finite

Focal Length Specification Wavelength (nm):
 980.00

Transmitted Wavefront Error (λ, RMS):
 < 0.200

Material Properties

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
 6.9

Environmental & Durability Factors

Operating Temperature (°C):
 ≤200

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)

Country of Origin:
 China

Imported By:
 Edmund Optics India Private Limited
 267, Greystone Building, Second Floor,
 6th Cross Rd, Binnamangala,
 Stage 1, Indiranagar, Bengaluru,

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information

