

[See all 7 Products in Family](#)

0.33 NA, 10.0mm FL, HOYA Molded Glass Aspheric Lens

See More by [Hoya](#)



HOYA Molded Glass Aspheric Lenses

Stock **#13-585** **20+ In Stock**

MRP ₹11,401

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹11,401 each
Qty 11-49	₹8,980 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**
A41_Z **Model Number:**

Physical & Mechanical Properties

8.00 +0.00/-0.02 **Diameter (mm):**

7.15 **Clear Aperture CA (mm):**

2.15 **Center Thickness CT (mm):**

Protective as needed **Bevel:**

Optical Properties

10.00 @ 780nm **Effective Focal Length EFL (mm):**

0.33 **Numerical Aperture NA:**

M-LAF81 **Substrate:**

780 **Aspheric Design Wavelength (nm):**

BBAR (755 - 805nm) **Coating:**

$R_{avg} < 1.5\%$ @ 755 - 805nm (theoretical per surface) **Coating Specification:**

1.25 **f#:**

40.5 **Abbe Number (v_d):**

1.731 **Index of Refraction (n_d):**

755 - 805 **Wavelength Range (nm):**

8.75 **Working Distance (mm):**

0 **Conjugate Distance:**

780 **Focal Length Specification Wavelength (nm):**

0.04 λ **Transmitted Wavefront, RMS @ 632.8nm:**

Material Properties

8.9 **Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}C$):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Thailand **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000 **Imported By:**

Product Details

- Precision Glass Molded Lenses
- Compact Sizes for Integration into Measurement Systems
- Multiple Glass Substrates Available

HOYAMolded Glass Aspheric Lenses are used in applications that require lenses with small sizes and high transmission that correct for spherical aberration. These aspheric lenses are manufactured through a patented molding process that produces precision aspheric surfaces to minimize wavefront error. Their small diameters and thicknesses allow for these molded aspheric lenses to be integrated into measurement systems, biomedical instrumentation, or other optical tools. HOYAMolded Glass Aspheric Lenses are available in multiple glass types that offer higher refractive indices and lower dispersion than other molded glass aspheric lens offerings.