

[See all 16 Products in Family](#)

TECHSPEC® 0.345X CobaltTL Telecentric Lens



Stock **#15-870** **2 In Stock**

MRP ₹2,82,416

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹2,82,416 each
Need More?	Request Quote

Product Downloads

General

CobaltTL Series **Product Family:**

Stock No. of Mounting Clamp:
#63-233- Sold Separately

Telecentric Lens **Type:**

Physical & Mechanical Properties

Variable	Iris Option:
195.50	Length (mm):
70.0	Maximum Diameter (mm):
975	Weight (g):
17.5	Flange Distance (mm):

Optical Properties

40.88mm	Horizontal Field of View, 1.1" Sensor:
37.16mm	Horizontal Field of View, 1" Sensor:
25.54mm	Horizontal Field of View, 2/3" Sensor:
20.89mm	Horizontal Field of View, 1/1.8" Sensor:
18.57mm	Horizontal Field of View, 1/2" Sensor:
17.60	Maximum Image Circle (mm):
0.034	Numerical Aperture NA, Object Side:
9 (7)	Number of Elements (Groups):
<0.094	Typical Telecentricity @ 588nm (°):
<0.088	Typical Distortion @ 588nm (%):
0.345X	Primary Magnification PMAG:
0.34	Telecentric Lens Magnification:
114	Working Distance (mm):
40.88 x 30.65	FOV @ Max Sensor Format, H x V (mm):
f/5 - f/16	Aperture (f/#):
425 - 675nm BBAR	Coating:
±4.435mm at f/10 (20% @ 20 lp/mm)	Depth of Field (mm):
0.345X	Magnification:
VIS	Lens Wavelength Range:

Sensor

1.1"	Maximum Sensor Format:
2.20	Pixel Size (µm):

Threading & Mounting

M67 x 0.75 (Female)	Filter Thread:
C-Mount	Mount:

Regulatory Compliance


View	Certificate of Conformance:
China	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details


- High Resolution Bi-Telecentric Lens with In-Line Illumination Options
- Up to 20 MegaPixels, 2.2 μ m Pixel Size
- 1.1", C-Mount Telecentric Lens with f /#s as Low as $f/4$

TECHSPEC® CobaltTL Telecentric Lenses are designed for semiconductor and electronics inspection, measurement, and gauging applications. These telecentric lenses achieve high light throughput with industry leading low f /#s. Featuring less than 0.015° telecentricity and low 0.013% distortion, these lenses are ideal for image stitching applications. These 17.6mm diagonal sensor format lenses are compatible with the Sony IMX304 1.1" sensors and other similar format sensors such as the Sony IMX183. TECHSPEC® CobaltTL Telecentric Lenses produce unparalleled levels of contrast yielding maximum image quality with the highest degree of measurement accuracy. In-line versions provide the ability to rotate/reposition the inline illumination port to allow for maximum flexibility when machine building. TECHSPEC® CobaltTL Telecentric Lenses are compatible with high vibration environments and feature a removable recessed set screw for securely locking the iris in place.


Technical Information




#15-870, 0.345X CobaltTL Telecentric Lens, Distortion Plot




#15-870, 0.345X CobaltTL Telecentric Lens, Relative Illumination Plot




#15-870, 0.345X CobaltTL Telecentric Lens, Telecentricity Plot




#15-870, 0.345X CobaltTL Telecentric Lens, Modulated Transfer Function (MTF) Plot, 114mm Working Distance, f5



#15-870, 0.345X CobaltTL Telecentric Lens, Depth of Field Plot, 114mm Working Distance, f5



#15-870, 0.345X CobaltTL Telecentric Lens, Modulated Transfer Function (MTF) Plot, 114mm Working Distance, f10



#15-870, 0.345X CobaltTL Telecentric Lens, Depth of Field Plot, 114mm Working Distance, f10

Description		Stock No.	Length (A)	Front Diameter (B)	Back Diameter (C)
0.28X	C-Mount	#62-921	197.59mm	138.6mm	50mm
0.36X	C-Mount	#88-602	163.5mm	70mm	43.5mm
0.5X	C-Mount	#62-911	172.9mm	90mm	50mm
0.55X	C-Mount	#88-603	182.5mm	62mm	43.5mm
0.69X	C-Mount	#15-872 / #15-873 (In-Line)	174.96mm	55mm	46mm
0.9X	C-Mount	#62-901	199.8mm	65mm	53mm