

[See all 8 Products in Family](#)

0.3mm Dia., TO-46 Package, InGaAs Photodiode



InGaAs Photodiodes (FC Receptacle , TO-5, TO-46)

Stock **#17-071** [CONTACT US](#)

1 MRP ₹11,257

Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-4 | ₹11,257 each |
| Qty 5-9 | ₹9,558 each |
| Qty 10-24 | ₹8,974 each |
| Need More? | Request Quote |

Product Downloads

General

Ball Lens **Type of Optics:**

InGaAs Photodiode **Type:**

1.5 **Rise/ Fall Time @ $V_R=5V$ (ns):**

Package:

Physical & Mechanical Properties

Active Area Diameter (mm):
0.3

Optical Properties

Spectral Response (nm):
900 - 1700

Electrical

Responsivity @ 1310nm (AW):
0.8 minimum / 0.9 typical

Responsivity @ 1550nm (AW):
0.9 minimum / 0.95 typical

Capacitance @ $V_R=5V$ (pF):
10 typical

Noise Equivalent Power NEP ($W/Hz^{1/2}$):
 6.28×10^{-15}

Maximum Forward Current (mA):
8

Maximum Reverse Current (mA):
2

Maximum Reverse Voltage (V):
15

Dark Current @ $V_R=5V$ (nA):
0.3 typical / 5 maximum

Regulatory Compliance

Certificate of Conformance:
[View](#)

Country of Origin:
United States

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Response Range From 900nm to 1700nm
- Both Small Area (High Speed) and Large Area
- [Segmented InGaAs Photodiodes](#) Also Available

InGaAs Photodiodes feature excellent responsivity from 900nm to 1700nm with active areas ranging from 0.07mm to 3.0mm. Photodiodes with active area sizes less than 1mm provide low capacitance, low dark current, and high responsivity from 1100nm to 1620nm, for high speed datacom and telecom applications. Photodiodes with active area sizes of 1mm and up provide large active areas, low noise, and high shunt resistance enabling high sensitivity for weak signals. InGaAs Photodiodes are isolated in TO-46, TO-18, or TO-5 packages with either a ball lens or double-sided AR coated window, depending on the packaging. These photodiodes are ideal for a multitude of research and OEM applications including IR laser alignment, medical diagnostics, and chemical analysis.

Note: To ensure well centered incident light, a [focusing lens](#) or [pinhole](#) is recommended due to inhomogeneity at the edge of the photodiode chip which can cause a decrease in detector responsivity.

Technical Information

