

[See all 2 Products in Family](#)

0.40 NA, 4.0mm FL, RPO IR Molded Glass Aspheric Lens



Stock #73-677 **20+ In Stock**

- 1 + MRP ₹13,621

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹13,621 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

10.00 ±0.025 **Diameter (mm):**

5.25 **Clear Aperture CA (mm):**

6.00 **Center Thickness CT (mm):**

Protective as needed **Bevel:**

Optical Properties

4.00 **Effective Focal Length EFL (mm):**

0.40 **Numerical Aperture NA:**

IG6 **Substrate:**

BBAR (800-1200) **Coating:**

Coating Specification:
R_{avg} <1% @ 800 - 1200, 0 - 30° AOI

80-60 **Surface Quality:**

0.4 **f#:**

800 - 1200 **Wavelength Range (nm):**

8.34 **Working Distance (mm):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Precision Infrared Glass Molded Lenses
- Ideal for High Volume Production Requirements
- Constructed with IG6 Infrared Glass Substrates

Rochester Precision Optics (RPO) Infrared Molded Glass Aspheric Lenses offer several key benefits, including high precision, >99% transmission, and improved performance by reducing optical aberrations, leading to smaller spot sizes and sharper images. Cost-effective molding processes enable options for high-quantity OEM integration while maintaining consistent specifications. Rochester Precision Optics (RPO) Infrared Molded Glass Aspheric Lenses are available with 4.00 and 6.50mm focal lengths and are AR coated for >99% transmission from 800 - 1200nm. Their lightweight form factor, small diameter, and reduced thickness allow these molded aspheric lenses to be integrated into cameras, aerospace systems, measurement systems, biomedical instrumentation, and handheld optical tools.

Note: Use of this substrate at elevated temperatures (>150C) or in the presence of some acids/bases can lead to formation of toxic compounds and should be avoided. Please see MSDS for details.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools