

0.420 - 1.08µm, 300mW, Silicon Power Detector



0.210 - 1.08µm, 11mW, Silicon Power Detector

Stock **#78-462** **1 In Stock**

1 MRP ₹2,25,675

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-4	₹2,25,675 each
Qty 5+	₹2,02,842 each
Need More?	Request Quote

Product Downloads

General

OD 1.0 Attenuator

Filters Included :

PH100-Si-HA-OD1-INT-D0

Model Number:

Integra (Integrated)

Compatible Meters:

Physical & Mechanical Properties

38.1 Dia. x27.4 T **Dimensions (mm):**

130 **Weight (g):**

0.13 **Weight (kg):**

10 **Active Area (mm):**

Optical Properties

420 - 1080 **Wavelength Range (nm):**

0.420 - 1.08 **Wavelength Range (μm):**

Sensor

Silicon **Type of Sensor:**

Electrical

300 **Maximum Incident Beam Power (mW):**

0.3 **Maximum Incident Beam Power (W):**

100 **Maximum Incident Power Density (W/cm^2):**

0.1 **Maximum Incident Power Density (kW/cm^2):**

10 pW **Noise Level:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Canada **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Photodetectors, Thermopiles, and Pyroelectric Detectors Available
- Various Active Area Sizes Across a Wide Range of Sensitivities
- [Meterless](#) and [Wireless](#) Detectors Also Available

Gentec-EO Integra USB Power and Energy Detectors combine a power meter and detector in one convenient package while providing fast response times and accurate measurements for beam analysis. These detectors are designed with a USB connector for easy connection to a PC or other acquisition system and include user-friendly software allowing for control via PC or serial commands. Versatile pyroelectric energy detectors with broadband coatings are optimized for low to high power densities. Gentec-EO Integra USB Power and Energy Detectors can be used with a variety of laser powers ranging from the nanowatts to multi-kilowatts. These detectors are ideal for laser energy measurement, thermal imaging, and remote sensing applications.