

[See all 76 Products in Family](#)

# LightPath 354240 | 9.94mm Dia., 0.50 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#37-102** **20+ In Stock**

[Other Coating Options](#)

1  MRP ₹9,989

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹9,989 each
Qty 11-49	₹8,980 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Thickness: 0.25 (t) (mm)  
Material: BK7

Compatible Window:

354240

Lightpath Lens Code:

Aspheric Lens

Type:

Typical Applications:  
Collimate or Focus Laser Light

## Physical & Mechanical Properties

Diameter (mm):  
9.94 ±0.015

Clear Aperture CA (mm):  
8

Edge Thickness ET (mm):  
1.44

Center Thickness CT (mm):  
3.43 ±0.05

Bevel:  
Protective as needed

Distance from Window to Lens (D) (mm):  
4.911

## Optical Properties

Effective Focal Length EFL (mm):  
8.00 @ 780nm

Numerical Aperture NA:  
0.50

Substrate:   
[D-ZK3](#)

Focal Length Tolerance (%):  
±1

Aspheric Design Wavelength (nm):  
780

Coating:  
BBAR (350-700nm)

Coating Specification:  
 $R_{avg} \leq 0.5\% @ 350 - 700nm$

Surface Quality:  
40-20

f#:  
1.00

Abbe Number ( $v_d$ ):  
50.22

Index of Refraction ( $n_d$ ):  
1.586

Wavelength Range (nm):  
350 - 700

Working Distance (mm):  
5.9

Conjugate Distance:  
Infinite

Focal Length Specification Wavelength (nm):  
780.00

Transmitted Wavefront Error ( $\lambda$ , RMS):  
< 0.08

## Material Properties

Coefficient of Thermal Expansion CTE ( $10^{-6}/^{\circ}C$ ):  
7.6

## Environmental & Durability Factors

Operating Temperature ( $^{\circ}C$ ):  
≤200

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 247:  
[Compliant](#)

Country of Origin:  
China

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



## Technical Information

