

[See all 77 Products in Family](#)

LightPath 355230 | 6.33mm Dia., 0.55 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-154** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

₹7,965

ADD TO CART

Volume Pricing	
Qty 1-10	₹7,965 each
Qty 11-49	₹7,020 each
Need More?	Request Quote

Product Downloads


General	
Thickness: 0.25 (t) (mm) Material: BK7	Compatible Window:
355230	Lightpath Lens Code:
Aspheric Lens	Type:

Typical Applications: Collimate or Focus Laser Light	
Physical & Mechanical Properties	
6.33 ±0.020	Diameter (mm):
5.07	Clear Aperture CA (mm):
1.67	Edge Thickness ET (mm):
2.71 ±0.05	Center Thickness CT (mm):
Protective as needed	Bevel:
2.834	Distance from Window to Lens (D) (mm):
Optical Properties	
4.51 @ 780nm	Effective Focal Length EFL (mm):
0.55	Numerical Aperture NA:
D-ZLaF52LA	Substrate: □
±1	Focal Length Tolerance (%):
780	Aspheric Design Wavelength (nm):
BBAR (600-1050nm)	Coating:
R _{abs} <1.0% @ 600 - 1050nm	Coating Specification:
40-20	Surface Quality:
0.91	f/#:
600 - 1050	Wavelength Range (nm):
3.08	Working Distance (mm):
Infinite	Conjugate Distance:
< 0.09	Transmitted Wavefront Error (λ, RMS):
Environmental & Durability Factors	
≤200	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:


Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information



;