

[See all 76 Products in Family](#)

# LightPath 354453 | 6mm Dia., 0.55 NA, BBAR (1050-1600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-159** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ MRP ₹7,567

📌 Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹7,567 each
Qty 11-49	₹6,810 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Thickness: 0.28 (t) (mm)  
Material: BK7

Compatible Window:

354453

Lightpath Lens Code:

Aspheric Lens

Type:

Typical Applications:  
Collimate or Focus Laser Light

## Physical & Mechanical Properties

Diameter (mm):  
6.00 ±0.020

Clear Aperture CA (mm):  
4.8

Edge Thickness ET (mm):  
1.75

Center Thickness CT (mm):  
3.14 ±0.02

Bevel:  
Protective as needed

Distance from Window to Lens (D) (mm):  
2.049

## Optical Properties

Effective Focal Length EFL (mm):  
4.60 @655nm

Numerical Aperture NA:  
0.55

Substrate:   
[D-ZK3](#)

Focal Length Tolerance (%):  
±1

Aspheric Design Wavelength (nm):  
655

Coating:  
BBAR (1050-1600nm)

Coating Specification:  
R<sub>abs</sub> <1.0% @ 1050 - 1600nm

Surface Quality:  
40-20

f#:  
0.91

Abbe Number (v<sub>d</sub>):  
60.88

Index of Refraction (n<sub>d</sub>):  
1.586

Wavelength Range (nm):  
1050 - 1600

Working Distance (mm):  
2.7

Conjugate Distance:  
Infinite

Focal Length Specification Wavelength (nm):  
655.00

Transmitted Wavefront Error (λ, RMS):  
< 0.09

## Material Properties

Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):  
7.6

## Environmental & Durability Factors

Operating Temperature (°C):  
≤200

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 247:  
[Compliant](#)

Country of Origin:  
China

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000


## Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



## Technical Information



## Compatible Mounts