

[See all 21 Products in Family](#)

## 0.5mm Diameter, Ruby Half-Ball Lens



Stock #49-557 **20+ In Stock**

- 1 + MRP ₹3,228

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹3,228 each
Qty 11-49	₹2,572 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Half-Ball Lens **Type:**

### Physical & Mechanical Properties

0.50 **Diameter (mm):**

0.25 **Radius R (mm):**

**Specific Gravity (g/cm<sup>3</sup>):**

3.98

Thickness (mm):

0.25

Compressive Strength (psi):

300,000

Diameter Tolerance ( $\mu\text{m}$ ):

$\pm 2.54$

## Optical Properties

Substrate:

Ruby Doped Sapphire ( $\text{Al}_2\text{O}_3$ )

Coating:

Uncoated

Index of Refraction ( $n_d$ ):

1.77

Sphericity ( $\mu\text{m}$ ):

0.64

## Environmental & Durability Factors

Melting Temperature ( $^{\circ}\text{C}$ ):

2053.00

## Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant

Country of Origin:

Switzerland

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Excellent for Severe Environments
- High Chemical Stability
- [Sapphire and Ruby Ball Lenses](#) Also Available

Sapphire and Ruby Half-Ball Lenses feature a very short back focal length with the convenience of a flat surface for easy mounting. Sapphire features a high index of refraction and excellent broadband transmission characteristics. Ruby half-ball (hemispherical) lenses are easier to see and, therefore, easier to handle for physical applications. Sapphire and Ruby Half-Ball Lenses are very chemically stable and are great for severe environments, high-temperature applications, and applications requiring high melting points. Typical applications include fiber communication, endoscopy, microscopy, optical pick-up devices, and laser measurement systems.

## Technical Information



