

[See all 76 Products in Family](#)

# LightPath 355392 | 4mm Dia., 0.60 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#83-627** **20+ In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ MRP ₹7,567

📌 Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹7,567 each
Qty 11-49	₹6,810 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

355392 **Lightpath Lens Code:**

Aspheric Lens **Type:**

Collimate or Focus Laser Light **Typical Applications:**

## Physical & Mechanical Properties

4.00 ±0.015	<b>Diameter (mm):</b>
3.6	<b>Clear Aperture CA (mm):</b>
1.34	<b>Edge Thickness ET (mm):</b>
2.24 ±0.02	<b>Center Thickness CT (mm):</b>
Protective as needed	<b>Bevel:</b>

## Optical Properties

2.75 @ 830nm	<b>Effective Focal Length EFL (mm):</b>
0.60	<b>Numerical Aperture NA:</b>
<a href="#">D-ZLaF52LA</a>	<b>Substrate:</b> <input type="checkbox"/>
±1	<b>Focal Length Tolerance (%):</b>
830	<b>Aspheric Design Wavelength (nm):</b>
BBAR (600-1050nm)	<b>Coating:</b>
R <sub>abs</sub> <1.0% @ 600 - 1050nm	<b>Coating Specification:</b>
40-20	<b>Surface Quality:</b>
0.78	<b>f#:</b>
40.79	<b>Abbe Number (v<sub>d</sub>):</b>
1.806	<b>Index of Refraction (n<sub>d</sub>):</b>
600 - 1050	<b>Wavelength Range (nm):</b>
1.5	<b>Working Distance (mm):</b>
Infinite	<b>Conjugate Distance:</b>
830.00	<b>Focal Length Specification Wavelength (nm):</b>
<0.16	<b>Transmitted Wavefront Error (λ, RMS):</b>

## Material Properties

6.9	<b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b>
-----	---

## Environmental & Durability Factors

≤200	<b>Operating Temperature (°C):</b>
------	------------------------------------

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>
China	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



## Technical Information

