

[See all 16 Products in Family](#)

TECHSPEC® 0.69X CobaltTL Telecentric Lens



Stock **#15-872** **2 In Stock**

⊖ 1 ⊕ ₹1,71,738

ADD TO CART

Volume Pricing	
Qty 1+	₹1,71,738 each
Need More?	Request Quote

Product Downloads

General

CobaltTL Series **Series:**

Stock No. of Mounting Clamp:
[#63-233](#)- Sold Separately

Telecentric Lens **Type:**

Physical & Mechanical Properties

Variable	Iris Option:
179.00	Length (mm):
175.00	Length excluding Threads (mm):
55	Maximum Diameter (mm):
796.9	Weight (g):

Optical Properties

20.39mm	Horizontal Field of View, 1.1" Sensor:
18.55mm	Horizontal Field of View, 1" Sensor:
12.75mm	Horizontal Field of View, 2/3" Sensor:
10.43mm	Horizontal Field of View, 1/1.8" Sensor:
9.27mm	Horizontal Field of View, 1/2" Sensor:
17.60	Maximum Image Circle (mm):
0.058	Numerical Aperture NA, Object Side:
9 (7)	Number of Elements (Groups):
0.69X	Primary Magnification PMAG:
0.69	Telecentric Lens Magnification:
110	Working Distance (mm):
20.4 x 15.3	FOV @ Max Sensor Format, H x V (mm):
f/4 - f/22	Aperture (f/#):
M4 MgF ₂	Coating:
±1.08mm at f/10 (20% @ 20 lp/mm)	Depth of Field (mm):
0.69X	Magnification:
<0.027	Typical Distortion @ 520nm (%):
<0.086	Typical Telecentricity @ 520nm (°):
VIS	Lens Wavelength Range:

Sensor

1.1"	Maximum Sensor Format:
2.20	Pixel Size (µm):

Threading & Mounting

M52 x 0.75 (Female)	Filter Thread:
C-Mount	Mount:

Regulatory Compliance

View	Certificate of Conformance:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:


Product Details

- High Resolution Bi-Telecentric Lens with In-Line Illumination Options
- Up to 20 MegaPixels, 2.2µm Pixel Size
- 1.1", C-Mount Telecentric Lens with f/#s as Low as f/4

TECHSPEC® CobaltTL Telecentric Lenses are designed for semiconductor and electronics inspection, measurement, and gauging applications. These telecentric lenses achieve high light throughput with industry leading low f/#s. Featuring less than 0.015° telecentricity and low 0.013% distortion, these lenses are ideal for image stitching applications. These 17.6mm diagonal sensor format lenses are compatible with the Sony IMX304 1.1" sensors and other similar format sensors such as the Sony IMX183. TECHSPEC® CobaltTL Telecentric Lenses produce unparalleled levels of contrast yielding maximum image quality with the highest degree of measurement accuracy. In-line versions provide the ability to rotate/reposition the inline illumination port to allow for maximum flexibility when machine building. TECHSPEC® CobaltTL Telecentric Lenses are compatible with high vibration environments and feature a removable recessed set screw for securely locking the iris in place.

Technical Information

Description		Stock No.	Length (A)	Front Diameter (B)	Back Diameter (C)
0.28X	C-Mount	#62-921	197.59mm	138.6mm	50mm
0.36X	C-Mount	#88-602	163.5mm	70mm	43.5mm
0.5X	C-Mount	#62-911	172.9mm	90mm	50mm
0.55X	C-Mount	#88-603	182.5mm	62mm	43.5mm
0.69X	C-Mount	#15-872 / #15-873 (In-Line)	174.96mm	55mm	46mm
0.9X	C-Mount	#62-901	199.8mm	65mm	53mm



The diagram shows a side view of a telecentric lens. Dimension A is the total length of the lens. Dimension B is the diameter of the front lens element. Dimension C is the diameter of the rear lens element. The lens has a complex multi-element design with various diameters and a central iris assembly.