

[See all 13 Products in Family](#)

Coherent® VLM™ Laser Diode 0220-923-00 | 0.6mW 635nm

See More by [Coherent®](#)



Coherent® VLM™ Laser Diode

Stock #54-032 **20+ In Stock**

MRP ₹25,700

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹25,700 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads



General

Index Guided Diode, CW **Type:**

Fully shielded, reverse polarity protected **Drive Circuitry:**

100000.00 **Diode Lifetime (hours):**

Type of Laser:

Diode

II **Laser Class - CDRH:**

Operating Lifetime (hours):
Standard 9V Battery: 5

Physical & Mechanical Properties

20.00 **Weight (g):**

+0, -0.0762 **Housing Tolerance (mm):**

914.4 **Length of Leads (mm):**

15.00 **Pointing Accuracy (arcmin):**

0.581 **Diameter (inches):**

1.776 **Length (inches):**

Optical Properties

635.00 **Wavelength (nm):**

±5 **Wavelength Tolerance (nm):**

0.2 - 0.3 **Wavelength Stability (nm/°C):**

<10 **Beam Astigmatism (µm):**

3.0 **Beam Diameter (mm):**

0.35 **Beam Divergence (mrad):**

Red **Color:**

Electrical

0.6 (Maximum) **Output Power (mW):**

±4 **Output Power Tolerance (%):**

ML Spec. Std. 1686B, Class 2 **ESD Protection:**

80 Typical, 100 Maximum **Current (mA):**

Hardware & Interface Connectivity

Power Supply:
Power Supply Required and Sold Separately.
USA: [#59-099](#)
Europe: [#35-201](#)
Japan: [#59-099](#)
Korea: [#33-771](#)
China: [#59-099](#)

5-10V DC **Power Requirement:**

red (+), black (-), case (+) **Electrical Leads/ Pin Connections:**

Free Space **Output Type:**

Environmental & Durability Factors

-10 to +40 **Operating Temperature (°C):**

-40 to +80 **Storage Temperature (°C):**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

Thailand **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor, **Imported By:**

Product Details

- Robust, High Quality Laser Diodes with Small Form Factor
- 635nm and 670nm High Visibility Wavelengths
- Sophisticated Electronic Design for Consistent Beam Properties

Coherent® Visible Laser Diode Modules feature a compact form factor to help users achieve space saving designs in systems that require a collimated light source. The simple design of these laser diodes allows for quick and efficient incorporation into a wide array of optical systems. A sophisticated electronic design aids in producing consistent laser power and beams. Coherent® Visible Laser Diode Modules with advanced AlignLock™ optical assembly technology provide a remarkable beam-pointing alignment of $<4.3\text{mrad}$, making these laser diodes a great choice for precision applications. These robust, compact laser diodes are typically used in machine vision, medical equipment, and many other industrial applications.

Note: [Power Supply](#), sold separately, is required for operation.

Technical Information

