

TECHSPEC® 0.75X, 110mm WD CompactTL™ Telecentric Lens



110mm WD, 0.75X, In-Line Version (Left) and VIS Version (Right)

Stock **#63-730** 10 TO 12 DAYS

⊖ 1 ⊕

₹35,078.00

ADD TO CART

Qty 1+

₹35,078.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length excluding Threads (mm):
156.20

Horizontal Field of View, 1/2" Sensor:
8.5mm

Horizontal Field of View, 2/3" Sensor:
11.7mm

Filter Thread:
M25.5 x0.50 (Female)

Maximum Diameter (mm):
29.5

Weight (g): 106
Horizontal Field of View, 1/3" Sensor: 6.4mm
Numerical Aperture NA, Object Side: 0.028
Working Distance Tolerance (mm): ±1
Number of Elements (Groups): 4 (4)
Note: CompactTL™
Typical Telecentricity @ 588nm (°): 0.096
Typical Distortion @ 588nm (%): 0.0211
Manufacturer: Edmund Optics®
Type: Telecentric Lens
Primary Magnification PMAG: 0.75X
Maximum Sensor Format: 2/3"
Working Distance (mm): 110
Mount: C-Mount
Aperture (f/#): f/13.3
Coating: λ/4 MgF ₂
Depth of Field (mm): ±1.2mm (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 11.7 x 8.8
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View