

[See all 12 Products in Family](#)

**TECHSPEC® 0.75X MercuryTL™ Liquid Lens Telecentric Lens**



0.75X MercuryTL™ Liquid Lens Telecentric Lens



Stock #73-701 **NEW** 14 In Stock

1 ₹2,08,800

**ADD TO CART**

Volume Pricing	
Qty 1+	₹2,08,800 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Mercury Series	<b>Series:</b>
MercuryTL™	<b>Note:</b>
Telecentric Lens	<b>Type:</b>
Liquid Lens Focusable	<b>Special Type of Lens:</b>

## Physical & Mechanical Properties

Length excluding Threads (mm):

146.21

Maximum Diameter (mm):

48.00

Weight (g):

222

## Optical Properties

Horizontal Field of View, 2/3" Sensor:

11.8

Horizontal Field of View, 1/2" Sensor:

8.5mm

Horizontal Field of View, 1/3" Sensor:

6.4mm

Typical Telecentricity @ 588nm (°):

<0.080

Typical Distortion @ 588nm (%):

<0.080

Primary Magnification PMAG:

0.75X

Telecentric Lens Magnification:

0.75

Working Distance (mm):

85 - 99

FOV @ Max Sensor Format, H x V (mm):

11.8 x 8.8

Aperture (f/#):

f/10

Depth of Field (mm):

±0.8 at f/10 (20% @20 lp/mm)

Wavelength:

VIS

## Sensor

Maximum Sensor Format:

2/3"

## Threading & Mounting

Mount:

C-Mount

## Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

China

Imported By:

Edmund Optics India Private Limited

## Product Details

- Liquid Lens for Extended Depth of Field Telecentric Lens
- Up to 2.3 MegaPixels, 4.5µm Pixel Size Sensors
- Up to 2/3", C-Mount Telecentric Lens
- Magnification from 0.15X to 0.75X

TECHSPEC® MercuryTL™ Liquid Lens Telecentric Lenses combine the capabilities of a telecentric lens with the flexibility of a liquid lens. These lenses combine the unique feature of telecentric lenses, eliminating parallax (or perspective) error, with a liquid lens, allowing for the focus to be electronically controlled. This combination provides quick working distance adjustment, while maintaining telecentricity, distortion, and image performance throughout the entire working distance range. TECHSPEC® MercuryTL™ Liquid Lens Telecentric Lenses are ideal for gauging, measurement, and placement applications where quick depth of field adjustment is required.

As the liquid lens is used to focus the telecentric lens, its curvature changes. As its curvature changes, there will be small changes in the ray angles in the rear of the lens (incident on the image sensor). As a result, there are small field of view changes over the working distance range as the liquid lens refocuses the lens. However, the front (object space) ray angles are unaffected by the liquid lens changing curvature, allowing the telecentric lens to maintain telecentricity over the entire working distance range.

**Note:** Hirose cables and [Liquid Lens Driver](#) sold separately.

## Technical Information

