

[See all 42 Products in Family](#)

TECHSPEC® 0.9 OD 25mm Dia., NIR ND Filter



Near-IR (NIR) Neutral Density (ND) Filters

Stock **#49-070** **4 In Stock**

- 1 + ₹8,486

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | ₹8,486 each |
| Qty 6-25 | ₹6,773 each |
| Qty 26-49 | ₹6,423 each |
| Need More? | Request Quote |

Product Downloads

General

Neutral Density Filter **Type:**

Physical & Mechanical Properties

25.00 +0.0/-0.2 **Diameter (mm):**

3.00 ±0.10 **Thickness (mm):**

80 Clear Aperture (%):

<5 Parallelism (arcsec):

Optical Properties

0.9 Optical Density OD (Average):

Fused Silica (Corning 7980) Substrate:

Metallic Based ND Coating:

40-20 Surface Quality:

12.5 Transmission (%):

700 - 1100 Blocking Wavelength Range (nm):

$\lambda/4$ Transmitted Wavefront, P-V:

± 10 Optical Density Tolerance (%):

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant REACH 241:

United States Country of Origin:

Edmund Optics India Private Limited Imported By:


Product Details

- Ideal for NIR Wavelengths 700-1100nm
- Optical Densities Ranging from 0.3 to 3.0

TECHSPEC® Near-IR (NIR) Neutral Density (ND) Filters feature a spectrally flat region between 700 and 1100nm, outstanding parallelism, and exceptional surface characteristics. The combination of high tolerance and broadband performance makes our filters ideal for attenuating a wide range of IR sources. The UV Fused Silica substrate features a low coefficient of thermal expansion and excellent surface quality, making these filters suitable for attenuating low power lasers, including lasers at the 1064nm Nd:YAG wavelength. Other applications include NIR spectroscopy, machine vision, and analytical chemistry. TECHSPEC Near-IR (NIR) Neutral Density (ND) Filters may be stacked to obtain a variety of optical densities. Orient the mirrored side toward the source at a 0° angle of incidence. Optical Densities of 0.5, 1.0, 1.5, 2.0, 2.5, and 3.0 are available in a [Pre-Loaded Filter Wheel](#).

Note: Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact kits@edmundoptics.com.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts
