

[See all 22 Products in Family](#)

**TECHSPEC® 0.9X, 28.7mm TFL-Mount PlatinumTL™ Telecentric Lens**



PlatinumTL™ Telecentric Lenses



Stock **#16-750** [CONTACT US](#)

⊖ 1 ⊕ **MRP ₹2,50,101**

ⓘ Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹2,50,101 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

PlatinumTL™ Series **Product Family:**

**Stock No. of Mounting Clamp:**  
#56-025 Sold Separately

Telecentric Lens **Type:**

## Physical & Mechanical Properties

Variable	Iris Option:
198.78	Length (mm):
65.0	Maximum Diameter (mm):
17.5	Flange Distance (mm):

## Optical Properties

24.9mm	Horizontal Field of View, APS-C Sensor:
31.9mm	Field of View, 28.7mm Sensor:
19.2mm	Horizontal Field of View, 4/3" Sensor:
15.8mm	Horizontal Field of View, 1.1" Sensor:
14.2mm	Horizontal Field of View, 1" Sensor:
9.8mm	Horizontal Field of View, 2/3" Sensor:
7.1mm	Horizontal Field of View, 1/2" Sensor:
28.70	Maximum Image Circle (mm):
0.045	Numerical Aperture NA, Object Side:
10 (7)	Number of Elements (Groups):
<0.070	Typical Telecentricity @ 588nm (°):
<0.035	Typical Distortion @ 588nm (%):
0.9X	Primary Magnification PMAG:
0.90	Telecentric Lens Magnification:
111.00	Working Distance (mm):
24.9 x 18.7	FOV @ Max Sensor Format, H x V (mm):
f/6 - f/22	Aperture (f/#):
425 - 675nm BBAR	Coating:
±0.65 at f/10 (20% @ 20 lp/mm)	Depth of Field (mm):
0.9X	Magnification:
VIS	Lens Wavelength Range:

## Sensor

APS-C	Maximum Sensor Format:
2.74	Pixel Size (µm):

## Threading & Mounting

M62 x 0.75 (Female)	Filter Thread:
TFL-Mount	Mount:

## Regulatory Compliance

<a href="#">Compliant</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Compliant</a>	REACH 241:

**Country of Origin:**

China

**Imported By:**


Edmund Optics India Private Limited  
 267, Greystone Building, Second Floor,  
 6th Cross Rd, Binnamangala,  
 Stage 1, Indiranagar, Bengaluru,  
 Karnataka, India 560038  
 Phone: +91-80-6845 0000

## Product Details


- High Resolution f/6 Bi-Telecentric Lens for Measurement
- Up to 35 MegaPixels, 2.8µm Pixel Size Sensors
- APS-C, C-Mount, T-Mount, F-Mount Telecentric Lens
- Magnification from 0.28X to 1.7X

TECHSPEC® PlatinumTL™ Telecentric Lenses are designed for semiconductor and electronics inspection, measurement, and gauging applications. The precision designs feature high telecentricity (<0.1°), low distortion (<0.1%), and high light throughput with an adjustable aperture that achieves f/6 when fully open. Capable of supporting large format 28.7mm diagonal sensors, these lenses are compatible with the Sony IMX342 APS-C sensor and other similar format sensors such as the Sony IMX530. TECHSPEC® PlatinumTL™ Telecentric Lenses produce unparalleled levels of contrast yielding maximum image quality with the highest degree of measurement accuracy. These lenses are suitable for high vibration environments and feature a removable recessed set screw for securing the iris in place.


## Technical Information




#16-750, 0.9X, 28.7mm TFL-Mount PlatinumTL™ Telecentric Lens, Distortion Plot




#16-750, 0.9X, 28.7mm TFL-Mount PlatinumTL™ Telecentric Lens, Relative Illumination Plot




#16-750, 0.9X, 28.7mm TFL-Mount PlatinumTL™ Telecentric Lens, Telecentricity Plot




#16-750, 0.9X, 28.7mm TFL-Mount PlatinumTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 111mm Working Distance, f6



#16-750, 0.9X, 28.7mm TFL-Mount PlatinumTL™ Telecentric Lens, Depth of Field Plot, 111mm Working Distance, f6



#16-750, 0.9X, 28.7mm TFL-Mount PlatinumTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 111mm Working Distance, f10



#16-750, 0.9X, 28.7mm TFL-Mount PlatinumTL™ Telecentric Lens, Depth of Field Plot, 111mm Working Distance, f10

Description		Stock No.	Flange	Length (A)	Front Diameter (B)	Back Diameter (C)
0.28X	C-Mount	#62-933	17.5mm	230.8mm	60.5mm	33.5mm
0.5X	C-Mount	#62-932	17.5mm	174.9mm	50mm	33.5mm
1.7X	C-Mount	#63-232	17.5mm	189.5mm	60mm	46mm
0.28X	F-Mount	#62-922	46.5mm	167.6mm	138.6mm	55mm
	M42 x 1.0	#62-923	6.56mm	208.5mm	138.6mm	50mm
	M42 x 1.0	#62-924	19.53mm	195.5mm	138.6mm	50mm
0.5X	F-Mount	#62-912	46.5mm	143mm	90mm	55mm
	M42 x 1.0	#62-913	6.56mm	184mm	90mm	50mm
	M42 x 1.0	#62-914	19.53mm	171.1mm	90mm	50mm
0.9X	F-Mount	#62-902	46.5mm	170.8mm	65mm	55mm
	M42 x 1.0	#62-903	6.56mm	210.7mm	65mm	53mm
	M42 x 1.0	#62-904	19.53mm	197.8mm	65mm	53mm

