

TECHSPEC® 0.9X CobaltTL Telecentric Lens



0.9X Magnification



Stock **#62-901** **1 In Stock**

1 MRP ₹2,20,668

 Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹2,20,668 each
Need More?	Request Quote

Product Downloads

General

CobaltTL Series **Product Family:**

Stock No. of Mounting Clamp:
#56-025 Sold Separately

Telecentric Lens **Type:**

Physical & Mechanical Properties

Length (mm):

199.80

Maximum Diameter (mm):

65.0

Weight (g):

862

Flange Distance (mm):

17.5

Optical Properties

Horizontal Field of View, 1.1" Sensor:

15.65mm

Horizontal Field of View, 1" Sensor:

14.23mm

Horizontal Field of View, 2/3" Sensor:

9.78mm

Horizontal Field of View, 1/1.8" Sensor:

8.00mm

Horizontal Field of View, 1/2" Sensor:

7.12mm

Maximum Image Circle (mm):

17.60

Numerical Aperture NA, Object Side:

0.075

Number of Elements (Groups):

10 (7)

Typical Telecentricity @ 588nm (°):

<0.089

Typical Distortion @ 588nm (%):

<0.014

Primary Magnification PMAG:

0.9X

Telecentric Lens Magnification:

0.90

Working Distance (mm):

111

FOV @ Max Sensor Format, H x V (mm):

15.8 x 11.6

Aperture (f/#):

f/6 - f/22

Coating:

425 - 675nm BBAR

Depth of Field (mm):

±0.33mm at f/10 (20% @ 20 lp/mm)

Magnification:

0.9X

Lens Wavelength Range:

VIS

Sensor

Maximum Sensor Format:

1.1"

Pixel Size (µm):

2.20

Threading & Mounting

Filter Thread:

M62 x 0.75 (Female)

Mount:

C-Mount

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

China

Imported By:


Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details


- High Resolution Bi-Telecentric Lens with In-Line Illumination Options
- Up to 20 MegaPixels, 2.2µm Pixel Size
- 1.1", C-Mount Telecentric Lens with $f/\#$ s as Low as $f/4$

TECHSPEC® CobaltTL Telecentric Lenses are designed for semiconductor and electronics inspection, measurement, and gauging applications. These telecentric lenses achieve high light throughput with industry leading low $f/\#$ s. Featuring less than 0.015° telecentricity and low 0.013% distortion, these lenses are ideal for image stitching applications. These 17.6mm diagonal sensor format lenses are compatible with the Sony IMX304 1.1" sensors and other similar format sensors such as the Sony IMX183. TECHSPEC® CobaltTL Telecentric Lenses produce unparalleled levels of contrast yielding maximum image quality with the highest degree of measurement accuracy. In-line versions provide the ability to rotate/reposition the inline illumination port to allow for maximum flexibility when machine building. TECHSPEC® CobaltTL Telecentric Lenses are compatible with high vibration environments and feature a removable recessed set screw for securely locking the iris in place.


Technical Information




#62-901, 0.9X CobaltTL Telecentric Lens, Distortion Plot



#62-901, 0.9X CobaltTL Telecentric Lens, Relative Illumination Plot




#62-901, 0.9X CobaltTL Telecentric Lens, Telecentricity Plot




#62-901, 0.9X CobaltTL Telecentric Lens, Modulated Transfer Function (MTF) Plot, 111mm Working Distance, f_6



#62-901, 0.9X CobaltTL Telecentric Lens, Depth of Field Plot, 111mm Working Distance, f6



#62-901, 0.9X CobaltTL Telecentric Lens, Modulated Transfer Function (MTF) Plot, 111mm Working Distance, f10



#62-901, 0.9X CobaltTL Telecentric Lens, Depth of Field Plot, 111mm Working Distance, f10

Description		Stock No.	Length (A)	Front Diameter (B)	Back Diameter (C)
0.28X	C-Mount	#62-921	197.59mm	138.6mm	50mm
0.36X	C-Mount	#88-602	163.5mm	70mm	43.5mm
0.5X	C-Mount	#62-911	172.9mm	90mm	50mm
0.55X	C-Mount	#88-603	182.5mm	62mm	43.5mm
0.69X	C-Mount	#15-872 / #15-873 (In-Line)	174.96mm	55mm	46mm
0.9X	C-Mount	#62-901	199.8mm	65mm	53mm