


## 0° AOI, 25mm Sq, UV Hot Mirror



UV Hot Mirrors

Stock **#46-588** **7 In Stock**

⊖ 1 ⊕ ₹11,755

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹11,755 each
Qty 10-25	₹10,588 each
Qty 26-49	₹10,043 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Shortpass Filter **Type:**

### Physical & Mechanical Properties

3.00 ±0.2 **Thickness (mm):**

25.0 x 25.0 ±0.5 **Dimensions (mm):**

90	Clear Aperture (%):
Seamed	Edges:
25.00	Length (mm):
25.00	Width (mm):

## Optical Properties

Dielectric	Coating Type:
Hot Mirror, 0°	Coating:
3 - 5λ	Surface Flatness (P-V):
245 - 1050	Wavelength Range (nm):
<a href="#">Fused Silica</a> (Corning 7980)	Substrate: <input type="checkbox"/>
0	Angle of Incidence (°):
R <sub>avg</sub> >70% @ 800 - 1050nm T <sub>avg</sub> >80% @ 245 - 460nm	Coating Specification:
80-50	Surface Quality:

## Regulatory Compliance

<a href="#">Compliant</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Compliant</a>	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:



## Product Details

- Transmits 80% of UV and Visible Light
- Reflects 70% of IR Light
- [Contact Us](#) for Custom Sizes

Designed for a 0° angle of incidence, these UV Hot Mirrors' multi-layer dielectric coating reflects infrared radiation, limiting heat buildup, while allowing UV and visible light to pass through. The fused silica substrate's high transmission is ideal for projection and illumination systems, as well as in fluorescence applications that require the transmission of the UV excitation wavelength and the rejection of radiation harmful to temperature sensitive samples.

Hot mirrors are crucial in many projection and illumination systems where high levels of heat can quickly damage sensitive components. Hot mirrors are specially coated to transmit visible light while reflecting the NIR, a major contributor to heat generation. By using a hot mirror, heat levels are limited with minimum impact on the overall system performance.

## Technical Information



**Quote Your Size**

**Compatible Mounts**

---