

## 0° AOI, 50mm Sq, UV Hot Mirror



UV Hot Mirrors

Stock #46-590 **20+ In Stock**

1  MRP ₹25,424

**Price inclusive of all taxes**

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹25,424 each
Qty 10-25	₹22,903 each
Qty 26-49	₹21,792 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Shortpass Filter **Type:**

### Physical & Mechanical Properties

3.00 ±0.2 **Thickness (mm):**

**Dimensions (mm):**

50.0 x 50.0 ±0.5

90 **Clear Aperture (%):**

Seamed **Edges:**

50.00 **Length (mm):**

50.00 **Width (mm):**

## Optical Properties

Dielectric **Coating Type:**

Hot Mirror, 0° **Coating:**

3 - 5λ **Surface Flatness (P-V):**

245 - 1050 **Wavelength Range (nm):**

**Substrate:**   
Fused Silica (Corning 7980)

0 **Angle of Incidence (°):**

**Coating Specification:**  
R<sub>avg</sub> >70% @ 800 - 1050nm  
T<sub>avg</sub> >80% @ 245 - 460nm

80-50 **Surface Quality:**

## Regulatory Compliance

**RoHS 2015:**  
Compliant

**Certificate of Conformance:**  
[View](#)

**Reach 247:**  
Compliant

United States **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000


## Product Details


- Transmits 80% of UV and Visible Light
- Reflects 70% of IR Light
- [Contact Us](#) for Custom Sizes

Designed for a 0° angle of incidence, these UV Hot Mirrors' multi-layer dielectric coating reflects infrared radiation, limiting heat buildup, while allowing UV and visible light to pass through. The fused silica substrate's high transmission is ideal for projection and illumination systems, as well as in fluorescence applications that require the transmission of the UV excitation wavelength and the rejection of radiation harmful to temperature sensitive samples.

Hot mirrors are crucial in many projection and illumination systems where high levels of heat can quickly damage sensitive components. Hot mirrors are specially coated to transmit visible light while reflecting the NIR, a major contributor to heat generation. By using a hot mirror, heat levels are limited with minimum impact on the overall system performance.

## Technical Information





**Quote Your Size**

**Compatible Mounts**

---