


[See all 6 Products in Family](#)

1" Dia. Maxi Black Labels, Low Outgassing Adhesive, 5 Labels

See More by [Acktar](#)



Acktar Die-Cut Light Blocking Black Labels



Stock **#29-031** **1 In Stock**

-

1

+

₹8,910

ADD TO CART

Volume Pricing	
Qty 1+	₹8,910 each
Need More?	Request Quote

Product Downloads

General	
MCBDC_25.4OD-3_ACK0030	Model Number:
Low Outgassing Adhesive	Type:
Note: Typical Adhesive Outgassing Performance: 0.85% TML, 0% VCM per ASTM E595-77/84/90	

Physical & Mechanical Properties	
75	Foil Thickness (µm):
60	Adhesive Thickness (µm):
Optical Properties	
MaxiBlack™	Coating:
4 - 6	Coating Thickness (µm):
0.3 - 5	Wavelength Range (µm):
Environmental & Durability Factors	
Moderate	Abrasion Resistance:
ML-C-48497A	Humidity Resistance:
-40 to +150	Operating Temperature (°F):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
Israel	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- 1" Diameter Labels Available in MaxiBlack™, Metal Velvet™, or Spectral Black™ Coatings
- Standard or Low Outgassing Adhesive Options
- 5 Labels Per Sheet
- Full Sheet and Rolls Available

Acktar Die-Cut Light Blocking Black Labels are used to eliminate reflection in applications where the direct coating of parts is not practical including optical packaging, laser devices and platforms, IR systems, or passive thermal control. All coatings feature high emissivity with low reflectance, excellent biocompatibility, a broad operating temperature range, and compatibility with class 1 cleanrooms. These die-cut products are offered in sheets of five, 1" (25.4mm) diameter adhesive-backed labels that can be used to quickly create a light blocking apparatus in a system by applying them to a surface or small optical mount. Acktar Die-Cut Light Blocking Black Labels are offered in Metal Velvet™ (diffusive coating on aluminum), Spectral Black™ (semi-specular coating on aluminum), or MaxiBlack™ (diffusive coating on polyimide), all with standard or low outgassing adhesive options. Metal Velvet offers superior light absorption performance while MaxiBlack, in addition to being durable and flexible, is nonconductive and can be used in applications that require light absorbing materials with no electrical conductivity.

Note: Metal Velvet has low resistance to abrasion and all surface contact should be avoided without proper equipment.