



[See all 6 Products in Family](#)

# 1" Dia. Maxi Black Labels, Standard Adhesive, 5 Labels

See More by [Acktar](#)



Acktar Die-Cut Light Blocking Black Labels



Stock **#29-030** [CONTACT US](#)

- 1 + ₹8,460

**ADD TO CART**

Volume Pricing	
Qty 1+	₹8,460 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

MCBDC\_25.4OD-1\_ACK0030 **Model Number:**

Standard Adhesive **Type:**

### Physical & Mechanical Properties

**Foil Thickness (µm):**

75

Adhesive Thickness (µm):

60

## Optical Properties

Coating:

MaxiBlack™

Coating Thickness (µm):

4 - 6

Wavelength Range (µm):

0.3 - 5

## Environmental & Durability Factors

Abrasion Resistance:

Moderate

Humidity Resistance:

ML-C-48497A

Operating Temperature (°F):

-40 to +121

## Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Compliant](#)

Country of Origin:

Israel

Imported By:

Edmund Optics India Private Limited

## Product Details

- 1" Diameter Labels Available in MaxiBlack™, Metal Velvet™, or Spectral Black™ Coatings
- Standard or Low Outgassing Adhesive Options
- 5 Labels Per Sheet
- [Full Sheet](#) and [Rolls](#) Available

Acktar Die-Cut Light Blocking Black Labels are used to eliminate reflection in applications where the direct coating of parts is not practical including optical packaging, laser devices and platforms, IR systems, or passive thermal control. All coatings feature high emissivity with low reflectance, excellent biocompatibility, a broad operating temperature range, and compatibility with class 1 cleanrooms. These die-cut products are offered in sheets of five, 1" (25.4mm) diameter adhesive-backed labels that can be used to quickly create a light blocking apparatus in a system by applying them to a surface or small optical mount. Acktar Die-Cut Light Blocking Black Labels are offered in Metal Velvet™ (diffusive coating on aluminum), Spectral Black™ (semi-specular coating on aluminum), or MaxiBlack™ (diffusive coating on polyimide), all with standard or low outgassing adhesive options. Metal Velvet offers superior light absorption performance while Maxblack, in addition to being durable and flexible, is nonconductive and can be used in applications that require light absorbing materials with no electrical conductivity.

**Note:** Metal Velvet has low resistance to abrasion and all surface contact should be avoided without proper equipment.